

# **Hardener Powder**

Standard hardener for 2-component, reactive DEGAROUTE  $^{\!\scriptscriptstyle (\!\scriptscriptstyle )}$  and DEGADUR  $^{\!\scriptscriptstyle (\!\scriptscriptstyle )}$  resin systems

### **Typical properties**

Property	Value	Unit	Method				
Form supplied	White, free-flow	White, free-flowing powder					
Odor	Virtually no odo	Virtually no odor					
Bulk density	0.64	g/cm <sup>3</sup>					
Active oxygen content	3.2 - 3.5	% by wt.					
Di-benzoyl-peroxide 50 % in phth	nalate						

#### **General remarks**

Accelerator	Is included in mostly DEGADUR® and DEGAROUTE® resins.				
Decomposition	SADT approx. 60 °C (heat accumulation to BAM = Bundesanstalt für Materialprüfung,				
temperature	Germany).				
Safety advice	Hardener powder may not be brought into direct contact with accelerators, spontaneous				
	decomposition is possible. See safety data sheet.				
Shelf life	6 months in original, unopened containers / from date of delivery				
Storage	Store at ≤ 25 °C. Protect against direct sunlight and humidity.				
Packaging	Carton with PE-inliner, 25 kg net				
Notes	Only following hardener (Di-benzoyl-peroxide) types from other manufacturers are				
	usable:				
	Benox BP-50-FT (Unided Initiators)				
	Perkadox GB-50X (Nouryon Polymer Chemistry)				
	PEROXAN BP-Pulver 50 W (Pergan GmbH)				
	NOVIPER BP50 (Novichem)				



# **DEGADUR®** Hardener Powder

### Hardener quantity for DEGADUR® resins with regard to temperature

	5 - 10 °C	10 - 15 °C	15 - 20 °C	20 - 25 °C	25 - 30 °C	>30 °C
	[%]	[%]	[%]	[%]	[%]	[%]
DEGADUR® B 71	6	5	4	3	2.5	2
DEGADUR® 111	2	1.5	1.2	1	0.7	0.7
DEGADUR® 112	5	4	3	2	1.5	1
DEGADUR® 115	6	4	3.5	3	2.5	2
DEGADUR® 117	5	4	3	2	2	1
DEGADUR® 151	4	3	2.5	2	2	1.5
DEGADUR® 332	5	4	3	2	2	1
DEGADUR® 418	4.5	3	2.5	2	2	1
DEGADUR® 419	4.5	3	2.5	2	2	1
DEGADUR® 420	4.0	2.5	2	1	1	1
DEGADUR® 430	5	4	3	2	2	1
DEGADUR® 510	6	4	3	2.4	2.4	1.2
DEGADUR® 163	2.5	2	2	1.5	1	
DEGADUR® 165	1.8	1.5	1	0.8	0.8	0.8
DEGADUR® 526	1.5	1.5	1.5	1	1	1
DEGADUR® 527	2	1.5	1.5	1.5	1	1
DEGADUR® 529	3.5	2.5	2	1.5	1.5	1
DEGADUR® 530	3.5	2.5	2	1.5	1.5	1

- 1. Peroxide quantity calculated on used resin. Temperature statements refer to resin-, floor- and air-temperature.
- 2. Quantity calculated on DEGADUR® 111 incorporating DEGADUR® F 111.

Note: All values are derived from laboratory tests. Deviations caused by environmental actors might occur.

Typical properties are approximate reference values. If you need product specifications please contact us.

® = registered trademark of Röhm or affiliates DEGADUR is a registered trademark of Röhm GmbH, Darmstadt, Germany.

This information and all further technical advice is based on our present knowledge and experience. However, it implies no liability or other legal responsibility on our part, including with regard to existing third party intellectual property rights, especially patent rights. In particular, no warranty, whether express or implied, or guarantee of product properties in the legal sense is intended or implied. We reserve the right to make any changes according to technological progress or further developments. The customer is not released from the obligation to conduct careful inspection and testing of incoming goods. Performance of the product described herein should be verified by testing, which should be carried out only by qualified experts in the sole responsibility of a customer. Reference to trade names used by other companies is neither a recommendation, nor does it imply that similar products could not be used.

Röhm GmbH
Dolivostraße 17
64293 Darmstadt
Germany
PHONE +49 6241 402-0

Roehm America LLC 299 Jefferson Road Parsippany, NJ 07054 USA PHONE +1 973 929-8000 Roehm Chemical (Shanghai) Co., Ltd. 55 Chundong Road, Xinzhuang Industry Park Shanghai 201108, China PHONE +86 21 61191 1616

Product Information 16.01.2020 Hardener Powder e Page 2/2